



More information on the website
mirror.radwag.com/en/info,w1,WYK

MAS.M.440.R2 Weighing Module

WX-016-0353



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	440 g
Preload range	44 g
Readability [d]	0.1 mg
Repeatability	0.35 mg
Linearity	±1 mg
Warm-up time after connection to power	1 h
Stabilization time	3.5 s
Adjustment	internal
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	Stainless steel
Communication interface	
Communication interface	RS232, max 115.2 kbps, Radwag ASCII protocol

Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 0.6A; 12V DC 1.2A Module: 12V DC
Environmental conditions	
Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%
Physical parameters	
Weighing pan dimensions	ø56 mm
Device dimensions W x D x H	232x126x125 mm
Net weight	1.6 kg



Accessories (Additional Fee)

RS 232, RS 485 cables
Antivibration Tables

R Terminal (WDM-8)

Software (Additional Fee)

• R-Panel [WX-010-0187]

Device dimensions W x D x H

