



More information on the website
mirror.radwag.com/en/info,w1,XXW

HX5.EX-1.6.H1 One Load Cell Platform Scale

WW-006-0019



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	6 kg
Minimum load	40 g
Readability [d]	2 g
Verification unit [e]	2 g
Tare range	-6 kg
OIML Class	III

Physical parameters		
Display		5" graphic colour
Cable length		1.5 m
Weighing pan dimensions		150×200 mm
Packaging dimensions W x D x H		310×640×460 mm
Net weight		11.5 kg
Gross weight		12.5 kg
Construction		
Protection class		IP 66 / 67 construction, IP 66 / 68 terminal
ATEX Certification		II 2G Ex ib IIB T4 Gb
IECEx Certification		Ex ib IIB T4 Gb
Construction		Stainless steel AISI304
Weighing pan material		Stainless steel AISI304
Communication interface		
Communication interface		2×RS232, RS485
Electrical parameters		
Power supply		100 – 240 V AC 50/60 Hz
Power consumption max.		15 W
Environmental conditions		
Operating temperature		-10 – +40 °C
Relative humidity		10% – 85% RH no condensation
Indicator		PUE HX5.EX-1



Additional fee for verification



Accessories (Additional Fee)

Communication Modules
Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX
Weighing Terminal

Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]