



More information on the website
mirror.radwag.com/us/info,w1,XXY

PUE 7.1.120.HRP High Resolution Scale

WP-350-0004



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| | |
|--------------------------------|----------------------------------|
| Maximum capacity [Max] | 120 kg |
| Minimum load | 50 g |
| Preload range | 30 kg |
| Readability [d] | 0,5 g |
| Tare range | -120 kg |
| Repeatability | 0,3 g |
| Linearity | ±2 g |
| Stabilization time | 3 s |
| Adjustment | internal (automatic) |
| Physical parameters | |
| Display | 5,7" Resistive Color Touchscreen |
| Weighing pan dimensions | 500×400 mm |
| Device dimensions W x D x H | 360×313×170 mm |
| Packaging dimensions W x D x H | 610×710×275 mm |
| Net weight | 37 kg |

| Physical parameters | |
|-------------------------|---|
| Gross weight | 52 kg |
| Construction | |
| Protection class | IP 66 / 67 construction, IP 43 terminal |
| Construction | mild steel St3S |
| Weighing pan material | Stainless steel AISI304 |
| Communication interface | |
| Communication interface | 2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi |
| Power supply | |
| Power supply | 100 – 240 V AC 50/60 Hz |
| Operating temperature | |
| Operating temperature | +10 – +40 °C |
| Relative humidity | |
| Relative humidity | 15% – 80% |

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

Displays

Transponder card readers
 Ethernet cables (scale - Ethernet)
 RS 232 cables (scale - printer)
 Barcode scanners

Label Printers


Receipt Printer
 AP2-1 Current Loop Unit
 Additional Weighing platforms Module
 RS 232 – USB Converter

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H



| Scale type | A1 | A2 | H |
|------------------------|------|------|-------|
| PUE7.1.16 - 32.HRP | 360 | 280 | 139±3 |
| PUE7.1.62 -120.HRP | 500 | 500 | 175±3 |
| PUE7.1.150 - 300.HRP | 800 | 600 | 175±3 |
| PUE7.1.300.1 -1100.HRP | 1000 | 800 | 175±3 |
| PUE7.1.2000.HRP | 1250 | 1000 | 175±3 |

dimensions in mm