



More information on the website
mirror.radwag.com/us/info,w1,YL5

MA 200/1.X7.IC.A Moisture Analyzer

WL-308-0035



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Statistics



IR sensors



GLP Procedures



Replaceable unit



Statistical Quality Control



ALIBI Memory



Drying modes



Samples drying



Moisture content
analysis



Dry mass determination



Wi-Fi

Datasheet

Maximum capacity [Max]	200 g
Readability [d]	0,1 mg
Tare range	-200 g
Adjustment	internal (automatic)
Maximum sample weight	200 g
Heating module	IR emitter
Moisture content repeatability	±0,05 % (sample ~ 2 g), ±0,01 % (sample ~ 10 g)
Moisture content readability	0,0001 %

Drying temperature range	Max 160 °C
Physical parameters	
Leveling system	manual
Display	7" graphic colour touchscreen
Weighing chamber	automatic
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions W x D x H	476×381×346 mm
Net weight	5,3 kg
Gross weight	6,8 kg
Construction	
Protection class	IP 43
Database capacity	Products, Users, Packaging, Customers, Drying programs, Drying process reports, Ambient Conditions, Weighings
Features of use	
Display mode	%D, %M, %R, g
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
Communication interface	RS232 ¹ , USB-A, USB-B, Ethernet, Wi-Fi
Power supply	100 – 120 V AC 50/60 Hz or 200-240 V AC 50/60 Hz
Power consumption	6 W
Heating module power	450 W
Operating temperature	+10 – +40 °C
Mass indication control	External mass standard 50g, 100g, 200g, depending on the type of moisture analyzer (additional equipment)
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (additional equipment: GT105k-12/Z Control Thermometer)
Drying temperature control	One- or two-point, depending on the drying profile (additional equipment: GT105k-12/Z Control Thermometer)
Moisture content indication control	Certified MV Test Set (additional equipment)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

Antivibration tables
Moisture analyzer accessories
Barcode scanners
Protective cover for balances

RS 232, RS 485 cables
Additional modules
RS 232 cables (scale - printer)
RS 232 – RS 485 Converter

Software (Additional Fee)

- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]
- E2R Moisture Analyzers [WX-010-0072]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions W x D x H

