



More information on the website  
[mirror.radwag.com/en/info,w1,YMJ](http://mirror.radwag.com/en/info,w1,YMJ)

# RTP-RU80 Radwag Thermal Receipt Printer (RS232 + USB)

WX-007-0119



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Paper width	80 mm
Print speed	max 300 mm/s
Roller external diameter	max 80 mm
<b>Communication interface</b>	
Communication interface	USB, RS232
<b>Electrical parameters</b>	
Power supply	100 – 240 V AC 50/60 Hz / 24 V DC 2.5 A
<b>Environmental conditions</b>	
Operating temperature	0 – +50 °C
Relative humidity	10% – 80%
<b>Physical parameters</b>	
Device dimensions	127×127×129 mm
Net weight	1.2 kg

## Compatible with (Additional Fee)

H315 HR Waterproof Platform Scale  
MA X7.IC.A Moisture Analyzer  
HX7 H Stainless steel Multifunctional Scale  
HX7.4N H Multifunctional Stainless Steel Ramp Scale  
HX7.4C Multifunctional Platform Scale  
HX7 HR Multifunctional Scale  
XA 5Y.M.A.P Microbalance for pipettes calibration  
WPY Multifunctional Scale  
MYA 5Y.P Microbalance for pipettes calibration  
AK-5/100.STENT Automatic Balance for Stents  
UMA 5Y.F Automatic Weighing System  
C32 Multifunctional Scale  
Stainless Steel HRP EX.H Platforms  
HX5.EX-1.4P2 H Stainless Steel Beam Scales  
HY10.HRP.H Stainless steel High Resolution Scale  
MA 5Y Moisture Analyzer  
C315 Platform scale  
5Y.PM Precision Balance  
MYA 5Y.F Microbalance for Filters  
HX5.EX-1 HR Stainless Steel 1-Load-Cell Platform Scales  
HX7.4P2 H Multifunctional Stainless Steel Beam Scales  
TMX H Stainless steel Multifunctional Scale  
WLY Scales for PGC  
MA X2.IC.A Moisture Analyzers  
AS X7 Analytical Balance  
PS X2 Precision Balance  
AS X2 PLUS Analytical Balances  
PS X7 Balances for PGC  
TMX Multifunctional Scale  
C315.D Baby Scale  
XA 5Y.M.A Microbalance  
WLC Precision Balance  
PS R2 Precision Balance  
C315.4P2 Beam Scales  
H315 4H Stainless Steel Platform Scale  
H315 4P2.H Stainless steel Beam Scales  
WLC X7 Precision Balance  
HX7.4N H.LD Multifunctional Stainless Steel Ramp Scale  
HX5.EX-1.4P2 C Beam Scales  
CY10 Scales for PGC  
PS X2 Balances for PGC  
DWT/RC/HYF Checkweighers  
H315 H Waterproof Platform Scale  
PUE CY10 Weighing Terminal  
CY10 Multifunctional Scale  
HX7.4P H Multifunctional Stainless Steel Pallet Scales  
MA X2.A Moisture Analyzers  
HX5.EX-1.4N Stainless Steel Ramp Scales  
HY10 Multifunctional Scale  
PUE 5 Weighing Terminal  
RS 232 cables (scale - printer)  
HX5.EX-1.4 C 4-Load-Cell Platform Scales  
HY10 H Stainless Steel Multifunctional Scale  
H315.4 H/Z Stainless Steel Platform Scale, pit version  
H315 4N.H Stainless Steel Ramp Scale  
PUE 7.1.HRP High Resolution Scale  
HRP EX Platforms High Capacity  
C315.4 Platform Scale  
HX5.EX-1.4P H Stainless Steel Pallet Scales  
HY10.HRP High Resolution Scale  
C32.PM Precision Balance  
Automatic Balances for. Pipettes Calibration  
HX7 Multifunctional Scale  
HX5.EX-1.4 H/Z Stainless Steel Platform Scales, Pit Version  
MA X7.A Moisture Analyzer  
HX7.4 H/Z Multifunctional Stainless Steel Platform Scale, pit version  
C315.O Personal Scale  
H315 4N.H.LD Stainless Steel Ramp Scale

UYA 5Y Ultra-Microbalance  
MA 5Y.IC Moisture Analyzer  
HX5.EX-1 C 1-Load-Cell Platform Scales  
MA R Moisture Analyzer  
HX5.EX-1 H Waterproof Platform Scales  
AS 5Y Analytical Balance  
AK-4 Automatic Mass Comparator  
PS 5Y Balances for PGC  
AKM-2 Automatic Mass Comparator  
PS R2.H Precision Balance  
PUE HX5.EX Weighing Terminal  
HY10.H Scales for PGC  
HX5.EX-1.4 H Stainless Steel 4-Load-Cell Platform Scales  
WTC Precision Balance  
CY10 Precision Balance  
RS 232, RS 485 cables  
H315 4C Platform Scale  
C315.OW Personal Scale  
XA 5Y.F Analytical Balance for Filters  
WLY Precision Balance  
UMA Automatic Mass Comparator  
H315 2K Overhead Track Scales  
APP 5Y.KO Manual Mass Comparator  
H315 4P.H Stainless Steel Pallet Scales  
Robotic Mass Comparators  
Density Measurement  
WLC C/2 Precision Balance  
MYA 5Y Microbalance  
H315 4I.S Livestock Scales  
PS R1 Precision Balance  
XA 5Y Analytical Balance  
Manual susceptometers - Magnetization  
5Y.PM.KB Manual Mass Comparator  
USB cable (scale - printer)  
AS R2 PLUS Analytical Balance  
PUE C32 Weighing Terminal  
PUE 7.1 Weighing Terminal  
PUE HX7 Weighing Terminal  
HRP 5Y.KO Mass Comparator  
PS 5Y Precision Balance  
Postal Scales for Packages  
Rotational Control Scales  
Automatic Vacuum Mass Comparators  
PMV 5Y Moisture Analyzer  
Automatic susceptometers - Magnetization  
HX5.EX-1.4P C Pallet Scales  
XA 5Y.KO Manual Mass Comparator  
DWM HPX Checkweighers  
HRP 5Y.KB Mass Comparator  
H315 4I.H Stainless Steel Livestock Scales  
XA 5Y.M Microbalance  
RMC F Robotic Weighing System  
PUE C315 Weighing Terminal  
RB F Robotic Weighing System  
PUE HY10 Weighing Terminal  
UYA 5Y.KO Manual Mass Comparator  
AS R1 PLUS Analytical Balance  
UYA 5Y.F Ultra-Microbalance for Filters  
Labelling Scales  
DWM H2 Checkweighers  
DWM/HPS Sorting Checkweigher  
C315.4B Bed Scale  
PUE H315 Weighing Terminal  
HX7.4P Multifunctional pallet scales  
Nano-Comparator NANO.AK-4.500.5Y  
DWM Checkweighers  
Control Scales for Large Loads  
C315.K Chair Scale

PS X7 Precision Balance  
WPY Scales for PGC  
XA 5Y.A Analytical Balance  
HX7.4 H Multifunctional Stainless Steel Platform Scale  
C315.4P pallet scales  
HX7.4P2 Multifunctional Beam Scales  
WAY 5Y.KO Manual Mass Comparator

Roller Scales  
XA 5Y.M.A.S Microbalance for stents weighing  
H315 Stainless Steel Overhead Track Scales  
AK-6 5Y.F Automatic Weighing System  
C315.8B Ramps Bed Scale  
Receipt Printer