



More information on the website  
[mirror.radwag.com/it/info,w1,YVH](http://mirror.radwag.com/it/info,w1,YVH)

# Sistema di pesatura su rotaia DWT/RC 300 HPK

WK-106-0017



The drawings, photos and graphics used are for illustrative purposes only.

## Specifiche

### Parametri metrologici

Portata massima [Max]	300 kg
Campo di tara	-300 kg

### Parametri fisici

Display	12" graphic colour touchscreen
---------	--------------------------------

### Components and software

Sistema operativo	Microsoft Windows 11 IoT
-------------------	--------------------------



## Accessori (Additional Fee)

Display  
 Lettore di tessere transponder  
 Cavo seriale RS 232 (connessione bilance - Stampanti ZEBRA)

Cavo seriale RS 232, RS 485  
 Stampanti di ricevuta  
 Cavo USB (connessione bilance - stampanti)