



More information on the website
mirror.radwag.com/it/info,w1,YVH

Sistema di pesatura su rotaia DWT/RC 300 HPK

WK-106-0017



The drawings, photos and graphics used are for illustrative purposes only.

Specifiche

Parametri metrologici

| | |
|-----------------------|---------|
| Portata massima [Max] | 300 kg |
| Campo di tara | -300 kg |

Parametri fisici

| | |
|---------|--------------------------------|
| Display | 12" graphic colour touchscreen |
|---------|--------------------------------|

Components and software

| | |
|-------------------|--------------------------|
| Sistema operativo | Microsoft Windows 11 IoT |
|-------------------|--------------------------|



Accessori (Additional Fee)

Display
 Lettore di tessere transponder
 Cavo seriale RS 232 (connessione bilance - Stampanti ZEBRA)

Cavo seriale RS 232, RS 485
 Stampanti di ricevuta
 Cavo USB (connessione bilance - stampanti)