

AS 120.R2 PLUS Analytical Balance

WL-104-0191





The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest

Dosing



Percent Weighing



Totalizing



Parts counting



Peak hold



Newton unit measurement



Statistics



Checkweighing

Density determination



Under-pan weighing



GLP Procedures



Animal weighing

Datasheet

Maximum capacity [Max]	120 g
Minimum load	1 mg
Readability [d]	0,01 mg
Verification unit [e]	1 mg
Tare range	-120 g
Standard repeatability [5% Max]	0,012 mg

Standard repeatability [Max]	0,03 mg
Standard minimum weight (USP)	24 mg
Standard minimum weight (U=1%, k=2)	2,4 mg
Permissible repeatability [5% Max]	0,02 mg
Permissible repeatability [Max]	0,05 mg
Linearity	±0,07 mg
Stabilization time	2 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	manual
Display	5,3" LCD (backlit)
Weighing chamber doors	manual
Delivery components	Balance, weighing pan, weighing pan shield, centring ring, bottom cover, power supply, fabric dust cover.
Weighing pan dimensions	ø90 open-work pan + ø85 (option) mm
Packaging dimensions W x D x H	545×455×575 mm
Net weight	7,04 kg
Gross weight	10 kg
Construction	
Protection class	IP 43
Communication interface	2×RS232¹, 2×USB-A (interchangeable), USB-B, Wi-Fi (option)
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Balance: 12 – 15V DC 0,4A max
Power consumption max.	3 W
Operating temperature	+10 - +40 °C
Relative humidity	40% - 80%
Notative Hullingty	7 0 /0

Repeatability is expressed as a standard deviation from 10 weighing cycles.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

 $[\]mbox{\ensuremath{^{\star}}}$ Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

Antivibration tables
Power Adapters
Cigarette lighter receptacle power supply cables
Density determination KIT
USB cable (scale - printer)
Professional Weighing Tables

RS 232, RS 485 cables Displays Protective cover for balances Weighing dishes Antistatic ionizer Receipt Printer


¹ Barcode scanners, available as weighing instrument accessory, communicate with the instrument via RS232 interface exclusively.

Software (Additional Fee)

- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]

- R Panel [WX-010-0187]
- RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H



AS R2, AS R1 d = 0.1 mg