



More information on the website  
[mirror.radwag.com/en/info,w1,ZEA](http://mirror.radwag.com/en/info,w1,ZEA)

# PL 3/6/D2 Platform

WX-009-1002



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	3 / 6 kg
Readability [d]	2 g
Construction	
Protection class	IP 43
Housing	ABS plastic
Weighing pan material	Stainless steel AISI304
Physical parameters	
Weighing pan dimensions	195×195 mm
Packaging dimensions W x D x H	530×310×150 mm
Net weight	2.7 kg
Gross weight	3.6 kg

**Readability accuracy** – expected value, dependent on the parameters of the measuring transmitter used.





## Accessories (Additional Fee)


CY10 Scales for PGC  
PUE CY10 Weighing Terminal  
CY10 Multifunctional Scale  
PUE 5 Weighing Terminal  
CY10 Precision Balance

PUE HX7 Weighing Terminal  
PUE C32 Weighing Terminal  
PUE 7.1 Weighing Terminal  
PUE HY10 Weighing Terminal  
RS 232 – USB Converter


# Device dimensions W x D x H




PL/D2



PLC/F1



PLC/C2  
PLC/C3



PL/H  
PL/HR

Platform type	A1	A2	H
PL/D2	238	216	82±3
PLC/F1	300	300	70±3
PLC/C2	402	502	103±3
PLC/C3	701	501	130±5
PL/H1 / PL/HR1	150	200	85±3
PL/H2 / PL/HR2	250	300	103±3
PL/H3 / PL/HR3	410	410	98±3
PL/H3/5 / PL/HR/3/5	400	600	155±3
PL/H4 / PL/HR4	500	500	155±3
PL/H5 / PL/HR5	600	600	155±3
PL/H6	800	800	135±3

dimensions in mm