



MYA 21.5Y Microbalance

WL-109-0010

More information on the website
mirror.radwag.com/us/info,w1,ZOC



The drawings, photos and graphics used are for illustrative purposes only.

Functions

- Autotest
- Dosing
- Percent Weighing
- Parts counting
- Peak hold
- Formulation
- Newton unit measurement
- Statistics
- Checkweighing
- IR sensors
- GLP Procedures
- Animal weighing
- Pipettes Calibration
- Air density correction
- Density determination
- Differential weighing
- Ambient conditions monitoring
- Statistical Quality Control
- Packaged Goods Control
- ALIBI Memory
- Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	21 g
Minimum load	0,1 mg

Metrological parameters	
Readability [d]	1 µg
Verification unit [e]	1 mg
Tare range	-21 g
Minimum weight (USP)	1,4 mg
Minimum weight (U=1%, k=2)	0,14 mg
Standard repeatability [5% Max]	0,7 µg
Permissible repeatability [5% Max]	1,6 µg
Linearity	±7 µg
Eccentric load deviation	7 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	3,5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø 90×90 mm
Weighing pan dimensions	ø26 mm
Packaging dimensions W x D x H	750×492×595 mm
Net weight	10,6 kg
Gross weight	16,5 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A Max; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max; 9 – 17W*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time dependson the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories (Additional Fee)

MediaBox

RFID Tags

Antivibration tables

Power Adapters

Adapters for pipettes calibration

Additional modules

Anti-Draft Chamber for Microbalances

Professional Weighing Tables

Antistatic ionizer

Protective cover for balances

Barcode scanners

Balance Storage Case

RS 232, RS 485 cables

Chamber for filter weighing

THBR 2.0 System - Ambient Conditions Monitoring

Weighing dishes

Receipt Printer

Fingerprint Reader

Adapter for Pipettes Calibration

RS 232 – USB Converter

Software (Additional Fee)

• E2R Weighing [WX-010-0099]

• Label Editor R02 [WX-010-0094]

• Scale Editor - EWAG 2.1 [WX-010-0173]

• RAD Key [WX-010-0005]

• RADWAG Remote Desktop [WX-010-0107]

• RADWAG Development Studio [WX-010-0104]

Device dimensions W x D x H

