



WAY 200.5Y.KO Mass Comparator

More information on the website
mirror.radwag.com/en/info,w1,ZQA



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
E1 Calibration Range	5 g ÷ 200 g
E2 Calibration Range	100 mg ÷ 200 g
F1 Calibration Range	1 mg ÷ 200 g
F2 Calibration Range	1 mg ÷ 200 g
M1 Calibration Range	1 mg ÷ 200 g
M2 Calibration Range	1 mg ÷ 200 g
Maximum capacity [Max]	210 g
Readability [d]	0.001 mg
Standard repeatability [5% Max]	3 µg
Standard repeatability [Max]	4 µg
Permissible repeatability	6 µg
Eccentricity (tested load)	0 mg*
Electric compensation range	-1 g ÷ +10 g
Stabilization time	30 s
Adjustment	internal

Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	ø40 mm
Weighing device dimensions	385×217×525 mm
Controlling device dimensions	249×170×72 mm
Anti-draft chamber dimensions	560×565×340 mm
Packaging dimensions	945×820×1260 mm
Chamber packaging size	860×830×840 mm
Net weight	22.5 kg
Gross weight	32.5 kg
Supplementary weights internal	automatic
Supplementary weights external	10 g
Communication interface	
Communication interface	2xUSB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Environmental conditions	
Operating temperature	+15 ÷ +30 °C
Operating temperature change rate	±0.5°C/12h (±0.3°C/4h)
Relative humidity	40% ÷ 60%
Relative humidity change rate	± 3 % / 4 h

Repeatability is expressed as a standard deviation determined for 6 ABBA cycles. Standard deviation is experimentally determined under ambient conditions for calibration of E1 class mass standards specified in OIML R111 (Table C.1.) document.

Eccentricity (tested load) – suspended self-centring weighing pan (available as an option): 0 mg

* **Eccentricity (tested load):** 1 d / mm

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories


RFID Tags
Antivibration Tables
Additional modules
Protective cover for balances
Barcode scanners
RS 232, RS 485 cables

Label Printers
THBR 2.0 System - Ambient Conditions Monitoring
Receipt Printer
Fingerprint Reader
RS 232, RS 485 cables
RS 232 cables (scale - printer)


Software

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]
- RMCS Lite [WX-010-0164]


Device dimensions




WAY 5.5Y.KO



WAY 100.5Y.KO



WAY 1200.5Y.KO



WAY 5100.5Y.KO