




MPS.T.3000.R1 Weighing Module

WX-016-0349

More information on the website
mirror.radwag.com/us/info,w1,ZUM



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	3000 g
Preload range	300 g
Readability [d]	0,1 g
Repeatability	0,1 g
Warm-up time after connection to power	1 h
Stabilization time	2 s
Adjustment	external
Construction	
Protection class	IP 43
Housing	aluminum
Weighing pan material	Stainless steel
Communication interface	
Communication interface	RS232, max 115,2 kbps, Radwag ASCII protocol

Electrical parameters

Power supply Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Module: 12V DC

Environmental conditions

Operating temperature +10 – +40 °C

Relative humidity 40% – 80%

Physical parameters

Weighing pan dimensions \varnothing 65 mm

Device dimensions W x D x H 220x70x75 mm

Net weight 0,9 kg



Accessories (Additional Fee)

RS 232, RS 485 cables
Antivibration tables

R Terminal (WDM-8)

Software (Additional Fee)

• R Panel [WX-010-0187]

Device dimensions W x D x H

